



Via Acquanera, 29 tel. 031.526.566 (r.a.) fax 031.507.984 info@calpower.it

22100 COMO www.calpower.it

Digitizer AL12250

- Single analog channel, two inputs switched by multiplexer (5 micro second switching time)
- AC/DC coupling, software selectable
- 50 Ohm input impedance/high input impedance software selectable
- Input ranges: 50 mVp-p 5Vp-p
- Fine offset control
- Time profile for gain control, 20 ns resolution, 10 bit gain control DAC

Bandwidth: DC to 100 MHz -3dB Input Coupling: AC or DC, software selectable



AL12250

The AL12250 is a single channel, non simultaneous dual input A/D board for the PCI bus. It is optimized for high-speed transient capture at sampling rates up to 250Msample/sec at very high repetition rates. A large dual-ported onboard buffer memory allows simultaneous transient recording and readout of captured data. A post-processing section can be used to extract peak information on multiple gates while the captured data is transferred over the PCI bus into the PC's main memory.

The analog inputs can be AC- or DC-coupled under software control. High input impedance (50 kOhms) or 50 Ohms termination are also software-selectable for high signal fidelity over the entire analog bandwidth of typically 100 MHz. Input voltage range can be set from 50 mV to 5V peak to peak.

An A/D converter with 8 bits resolution samples the input signal at 250 Msample/sec. The sampled data is stored in an onboard memory buffer of 128 Msamples. The size of this buffer memory determines the maximum length of an acquisition. The board will be ready to accept a trigger about 2 microseconds after the end of the previous acquisition, which allows for repetition rates well beyond 100 KHz for short acquisitions.

The sampling clock is generated on the board or can be accepted from an external source in the form of a frequency reference of 5.0 or 10.0 MHz or as a direct sampling clock. Decimating the sampled data while reading it from the buffer memory creates lower sampling rates. Reading data from the buffer memory occurs simultaneously with acquisition and does not affect repetition rate.

The sampled data is transferred over the PCI bus using DMA, thus requiring no CPU intervention to achieve high transfer rates. During this data transfer, a set of peak detectors can be used to monitor the sample stream and extract peak position and threshold crossing data over selected regions (gates) of the sampled data.

A large selection of flexible triggering modes allows the user to tailor the behavior of the board to many applications. In addition to the standard software-generated trigger, the board can be triggered by a threshold crossing of the analog input signal on any channel or a signal fed to the BNC Trigger connector, a digital TTL signal on the internal trigger connector or a position-derived trigger from an encoder or motor of a scanning system.

The BNC Trigger connector can also drive a trigger signal as an output; for instance, to fire an ultrasonic pulser/receiver. This driver supports special modes that can be used to trigger multiple boards simultaneously from any of the connected boards, simply by tying the BNC Trigger connectors together.

A simple oscilloscope program is included with the board. It allows evaluation of the various configurations and triggering modes of this board. Drivers and a DLL are provided to access functionality of the board from a user application.

The internal sampling clock is generated by a PLL, multiplying a 5 MHz reference up to 400 MHz. From an external source the sampling clock can either be fed in directly from an external 400 MHz source or multiplied up by the PLL from an external 10 or 5 MHz reference input. In either case the sampling will be coherent with the external input clock. Many other reference input frequencies are possible – any multiple of 500 KHz from 5 to 50 MHz.

A/D Converter	Clock
♦ 250 MSamples/sec sampling rate	Sampling rates: 250 MHz, 125 MHz, 62.5 MHz
12 bits resolution, single channel	Trigger Sources
	 Software trigger Encoder trigger Internal trigger connector TTI
	 External trigger input, programmable threshold (BNC) Signal threshold trigger, programmable threshold

	Trigger Output
	TTL output, 2V into 50 or 25 Ohms
	programmable polarity
Trigger Sources	pulse indicates beginning and end of acquisition
 Software trigger Internal trigger connector, TTL, programmable polarity (3 pin header) External trigger input (BNC trigger connector), 	Acquisition Control
	Pre-trigger and Post-trigger delay acquisition
	26 bit pre/post-trigger and length counters
	Auto re-arming
	Interrupt after programmable number of acquisitions
programmable threshold -5.0V +5.0V and polari-	Memory
 ty, 50 Ohm / 1 kOhm input impedance software selectable Signal threshold trigger, programmable threshold and polarity. Encoder position trigger, for scanning applications 	MSamples on-board acquisition memory, dual-ported
	Fast offload while acquiring
	Optimized for maximum repetition rate in both pre- and post-trigger modes
	DSP Functions
	Multiple acquisitions per trigger
	On-board peak detection with up to 100 gates
	Customized processing functions available through firmware upload
	Bus Interface
	PCI interface, 32 bits, 33 MHz
	PCI master mode operation
	PCI burst transfer rates up to 133 MBytes/sec
	DMA transfers with scatter/gather support
	Interrupt on completion of DMA transfers
	Connectors
	2-BNC connectors for analog signal input
	BNC connector for clock/reference input/output
	PCI master mode operation
	DMA transfers with scatter/gather support
Cal Power	BNC female connectors
/ia Acquanera, 29 22100 COMO el. 031.526.566 (r.a.) fax 031.507.984 nfo@calpower.it www.calpower.it	Physical Dimensions
	Full height, half length PCI board (176mm x 100mm)

Full height, half length PCI board (176mm x 100mm)